

CCT Function

- These kits are supplied with removable and interchangeable heads. For 73347, 73348, 73349 and 99765, it is possible to choose between warm white (3000K) and cool white (4000K) light output. For 76615, 76616 and 76617, it is possible to choose between daylight white (6500K) and blue light (20000K) output.
- To change colour you simply turn the LED head 180° and reinsert back into the loom, according to the arrows on the connector as detailed below and in **Fig. E**.
- **73347/73348/73349/99765**
 - Arrow on LED head unit is connected to arrow 1 on connector = Warm white (3000K)
 - Arrow on LED head unit is connected to arrow 2 on connector = Cool white (4000K)
- **76615/76616/76617**
 - Arrow on LED head unit is connected to arrow 1 on connector = Daylight white (6500K)
 - Arrow on LED head unit is connected to arrow 2 on connector = Blue light (20000K).

